

AGAR CORPORATION

Process Measurement & Control



ID 200 Series

Interface Concentration Detector System

SYSTEMS: ID-201 (½ Inch Shaft)
ID-202 (1 ¼ Inch Shaft)
ID-205 (Cable mounted)

Description

The *ID-200 Series Interface Detectors* are used for interface measurement and control in all types of liquid/liquid and vapor/liquid separation processes including emulsions and foam. A wide range of models, process connections, and output options are available for the control of a variety of process installations such as Tanks, Decanters, Dehydrators, Desalters, Coalescers, etc. The *ID-200 Series* advanced control capabilities can be used to automate upset responses, antifoam and demulsifier chemical feed systems, and eliminate cross-contamination of separating phases.

Operating Range

Emulsion Concentration:	0-100% Hydrocarbon/ Water by Volume
Process Temperature:	Standard: 32°F to 300°F (0°C to 149°C) High-Temp: 32°F to 450°F (0°C to 232°C)
Ambient Temperature:	-40°F to 131°F
Pressure Rating:	Up to 3000 PSI

Materials Of Construction

Probe:	Standard:	316 Stainless Steel, Teflon & Peek
	Optional:	Duplex, Hastalloy, Monel (Others available on request)
Seals:	Standard:	Aflas and Teflon
	Optional:	Viton

NACE compliant

Optional Process Connection

SH-2"/SS:	2" NPT Seal Housing, 316 Stainless Steel
SH-2"/CS:	2" NPT Seal Housing, Carbon Steel
CF-3/4"/SS:	3/4" NPT Compression Fitting, 316 Stainless Steel
CF-3/4"/CS:	3/4" NPT Compression Fitting, Carbon Steel
Flanged Connections:	ANSI 150# to 1500#



ID-201 Components: Probe, Seal Housing & Power Supply Nema 4/7 Enclosure

www.agarcorp.com

Model Variations

ID-201:	1/2" shaft	Standard: 48" (4 Ft.)	Minimum: 12" (1 Ft.)	Maximum: 120" (10 Ft.)
ID-202:	For probe lengths greater than 10 feet, sturdier 1-1/4" shaft assemblies from five foot sections via threaded connections.			
ID-205:	Shaft replaced by cable for suspension of antenna down through the top of the tanks, wells, platform legs, caverns, etc.			

Electrical Rating

ID-201, ID-202, ID-205 Probe	Intrinsically Safe: Class 1, Div.1, Groups C & D, T3C ATEX:  II 1G EEx ia IIB T4 (-40°C<Ta<+70°C)  II 1G EEx ia IIC T5 (-40°C<Ta<+65°C)
Power Required:	115/240 VAC 50-60 Hz or 12/24 VDC (±20%); Normal Power Consumption 3 Watts Maximum Power Consumption of 250 Watts (including lights)
PS-201 Enclosures:	Weatherproof (N4X) NEMA 4X Explosion Proof (N4/7) NEMA 4/7 Class 1, Div. 1, Groups C&D Flame-Proof (N4/7) NEMA 4/7 ATEX:  II 2G Ex d[ia] IIB T6 (-20°C<Ta<+55°C)
Wiring Connections:	Barrier Terminal Block #18 AWG Maximum Diameter

Standard Output Options

ID-201/420:	Powered 4-20 mA into 400 Ohms Maximum; 4 mA = Oil, or Lowest Water Content
ID-201/RL:	Relay Contact 1A; 115V; NO and NC; (SPDT); Fail Safe On Water or Oil; Adjustable Trip Point
ID-201/RL/420:	Relay and 4-20mA Options
ID-201/RL/LI:	Relay with Local Indicating Lights; Amber = Oil, Blue = Water

CERTIFICATIONS

CSA-US Canadian Standards Association /UL Specifications
ATEX European Committee for Electrical Standardization
GOST-R Russian Approval, ROSTECHNADZOR Safety
JRIIS Japanese Research Institute of Industrial Safety

HEADQUARTERS - CAYMAN ISLAND: Agar Corporation, LTD • P.O. Box 10206 • Grand Cayman, BWI KY1-1002 • Tel: (345) 945-5242 • ACL@agarcorp.com

	USA Agar Corporation; 5150 Tacoma Drive; Houston, TX 77041; Tel: (832) 476-5100; Fax: (832) 476-5299; ACI@agarcorp.com
	CANADA Agar Canada Corp; Unit 120, 3510 29th St NE; Calgary, AB T1Y7E5; Tel: (403) 718-9880; Fax: (403) 450-8350; Sales@agarcorp.ca
	COLOMBIA Agar Colombia; SAS Carrera 19 No. 19-13, Of. 304; Bogotá, Colombia; Tel: +57 1 646-965; Ventas@agarcolombia.co
	ECUADOR Agarcorporation Ecuador C.A.; Av. 12 de Octubre; N24-739 y Av. Colon Edif. Torre Boreal; Piso 6, Oficina 609; Quito Ecuador; Tel: +593 2 6007370; Ventas@rcorpecuador.com
	INDONESIA Pt Agar Indonesia; JL Rafflesia No. 3 Blok C A19 Ciputat Baru; 15413 Ciputat Indonesia; Tel: +62-21-740-9210; PTAI@agarcorp.com
	MALAYSIA Agarcorp Sdn Bhd, ACSB; Jalan 5/106, Bandar Sri Permaisuri; A-4-1, Plaza Dwtasik; 56000 Kuala Lumpur; Malaysia; Tel: +603-9171 7069; Fax: +603-9173 8069; ACSB@agarcorp.com
	SAUDI ARABIA - Al Khobar Agar Corporation Ltd; Nayef Building no-01 (Flat no -10); Prince Nayef Street/22nd St cross; Al Shamaliyah, Al Khobar; Saudi Arabia; Tel: 966-501066418; ACSA@agarcorp.com
	SAUDI ARABIA - Jeddah Agar Corporation Ltd; Al Faisaliyah Building; Imam Abdul Aziz Street; Jeddah - 21753; Saudi Arabia; Tel: 966-501066418; ACSA@agarcorp.com
	UAE Agar Corporation (ACAD); 1505, Three Sails Tower; Corniche, Khalidiya; Abu Dhabi, UAE; Tel: 971-2681-1150; ACAD@agarcorp.com
	VENEZUELA Agarcorp de Venezuela C.A.; Avenida Jesus Subero; El Tigre, Anzoategui; 6050 Venezuela; Tel: +58-261-324-5789; ADV@agarcorp.com

AGAR CORPORATION

© Agar Corporation Inc. All rights reserved. Specifications may be changed without notice.

www.agarcorp.com

ER No. 5485: ACI-A-7.2-DOC-006 Rev 01